

General Specifications

GS 33J01N21-01EN

Contents of A2FVX1 A2NBX1 and A2CUX1
A2FVX1 Field Control Kit
A2NBX1 FIO Node Kit
A2CUX1 AEPV7D Input Power Cable Kit
(for A2CUKT4)



[Release 6]

■ GENERAL

This General Specifications (GS) describes contents of the model for ordering multi-products. The contents are listed according to MS-CODE.

For A2FVX1, A2NBX1 and A2CUX1, please refer to GS 33J01N20-01EN.

The model for ordering multi-products

Model	Name
A2FVX1	Field Control Kit
A2NBX1	FIO Node Kit
A2CUX1	AEPV7D Input Power Cable Kit (for A2CUKT4)

■ CONTENTS OF THE MODEL FOR ORDERING MULTI-PRODUCTS

● Field Control Kit A2FVX1

A2FVX1-□□1□□□ (100-120 V AC)

Contents of the model for ordering multi-products				A2FVX1-□□1□□□ MS-CODE					
Category	Model	MS-CODE	Description	A2FVX1-D01000/HKU A2FVX1-S01000/HKU	A2FVX1-D01000 A2FVX1-S01000	A2FVX1-D01010/HKU A2FVX1-S01010/HKU	A2FVX1-D01010 A2FVX1-S01010	A2FVX1-D01100 A2FVX1-S01100	A2FVX1-D01110 A2FVX1-S01110
Base Plate	A2BE1D	-S000	no explosion protection	1	1				
		-S010	no explosion protection/G3			1	1		
		-S100	explosion protection					1	
		-S110	explosion protection/G3						1
HKU inter face unit	A2FU1	-00	no explosion protection	1					
		-10	no explosion protection/G3			1			
Primary power distribution unit	A2FU2	-1100	100-120 V AC		1			1	
		-1110	100-120 V AC/G3				1		1
		-2100	220-240 V AC						
		-2110	220-240 V AC/G3						
		-4100	24 V DC						
		-4110	24 V DC/G3						
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection	1 / 2	1 / 2				
		-51	100-120 V AC /no explosion protection/G3			1 / 2	1 / 2		
		-E0	100-120 V AC/explosion protection					1 / 2	
		-E1	100-120 V AC/explosion protection/G3						1 / 2
	PW482	-50	220-240 V AC /no explosion protection						
		-51	220-240 V AC /no explosion protection/G3						
		-E0	220-240 V AC/explosion protection						
		-E1	220-240 V AC/explosion protection/G3						
	PW484	-50	24 V DC /no explosion protection						
		-51	24 V DC /no explosion protection/G3						
		-E0	24 V DC /explosion protection						
		-E1	24 V DC /explosion protection/G3						
Processor Module	CP471	-00	no explosion protection	1 / 2	1 / 2				
		-01	no explosion protection/G3			1 / 2	1 / 2		
		-10	explosion protection					1 / 2	
		-11	explosion protection/G3						1 / 2
Dummy Cover	ADCV01		For slot C2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC /no explosion protection/ HKU	100-120 V AC /no explosion protection	100-120 V AC /no explosion protection/G3/ HKU	100-120 V AC /no explosion protection/G3	100-120 V AC/explosion protection	100-120 V AC/explosion protection/G3

A2FVX1-□□2□□□ (220-240 V AC)

Contents of the model for ordering multi-products				A2FVX1-□□2□□□ MS-CODE					
Category	Model	MS-CODE	Description	A2FVX1-D02000/HKU A2FVX1-S02000/HKU	A2FVX1-D02000 A2FVX1-S02000	A2FVX1-D02010/HKU A2FVX1-S02010/HKU	A2FVX1-D02010 A2FVX1-S02010	A2FVX1-D02100 A2FVX1-S02100	A2FVX1-D02110 A2FVX1-S02110
Base Plate	A2BE1D	-S000	no explosion protection	1	1				
		-S010	no explosion protection/G3			1	1		
		-S100	explosion protection					1	
		-S110	explosion protection/G3						1
HKU inter face unit	A2FU1	-00	no explosion protection	1					
		-10	no explosion protection/G3			1			
Primary power distribution unit	A2FU2	-1100	100-120 V AC						
		-1110	100-120 V AC/G3						
		-2100	220-240 V AC		1			1	
		-2110	220-240 V AC/G3				1		1
		-4100	24 V DC						
		-4110	24 V DC/G3						
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection						
		-51	100-120 V AC /no explosion protection/G3						
		-E0	100-120 V AC /explosion protection						
		-E1	100-120 V AC /explosion protection/G3						
	PW482	-50	220-240 V AC /no explosion protection	1 / 2	1 / 2				
		-51	220-240 V AC /no explosion protection/G3			1 / 2	1 / 2		
		-E0	220-240 V AC /explosion protection					1 / 2	
		-E1	220-240 V AC /explosion protection/G3						1 / 2
	PW484	-50	24 V DC /no explosion protection						
		-51	24 V DC /no explosion protection/G3						
		-E0	24 V DC /explosion protection						
		-E1	24 V DC /explosion protection/G3						
Processor Module	CP471	-00	no explosion protection	1 / 2	1 / 2				
		-01	no explosion protection/G3			1 / 2	1 / 2		
		-10	explosion protection					1 / 2	
		-11	explosion protection/G3						1 / 2
Dummy Cover	ADCV01		For slot C2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC /no explosion protection/ HKU	220-240 V AC /no explosion protection	220-240 V AC /no explosion protection/G3/ HKU	220-240 V AC /no explosion protection/G3	220-240 V AC/explosion protection	220-240 V AC/explosion protection/G3

A2FVX1-□□4□□□ (24V DC)

Contents of the model for ordering multi-products				A2FVX1-□□4□□□ MS-CODE					
Category	Model	MS-CODE	Description	A2FVX1-D04000/HKU A2FVX1-S04000/HKU	A2FVX1-D04000 A2FVX1-S04000	A2FVX1-D04010/HKU A2FVX1-S04010/HKU	A2FVX1-D04010 A2FVX1-S04010	A2FVX1-D04100 A2FVX1-S04100	A2FVX1-D04110 A2FVX1-S04110
Base Plate	A2BE1D	-S000	no explosion protection	1	1				
		-S010	no explosion protection/G3			1	1		
		-S100	explosion protection					1	
		-S110	explosion protection/G3						1
HKU inter face unit	A2FU1	-00	no explosion protection	1					
		-10	no explosion protection/G3			1			
Primary power distribution unit	A2FU2	-1100	100-120 V AC						
		-1110	100-120 V AC/G3						
		-2100	220-240 V AC						
		-2110	220-240 V AC/G3						
		-4100	24 V DC		1			1	
		-4110	24 V DC/G3				1		1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection						
		-51	100-120 V AC /no explosion protection/G3						
		-E0	100-120 V AC /explosion protection						
		-E1	100-120 V AC /explosion protection/G3						
	PW482	-50	220-240 V AC /no explosion protection						
		-51	220-240 V AC /no explosion protection/G3						
		-E0	220-240 V AC /explosion protection						
		-E1	220-240 V AC /explosion protection/G3						
	PW484	-50	24 V DC /no explosion protection	1 / 2	1 / 2				
		-51	24 V DC /no explosion protection/G3			1 / 2	1 / 2		
		-E0	24 V DC /explosion protection					1 / 2	
		-E1	24 V DC /explosion protection/G3						1 / 2
Processor Module	CP471	-00	no explosion protection	1 / 2	1 / 2				
		-01	no explosion protection/G3			1 / 2	1 / 2		
		-10	explosion protection					1 / 2	
		-11	explosion protection/G3						1 / 2
Dummy Cover	ADCV01		For slot C2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				24 V DC /no explosion protection/ HKU	24 V DC /no explosion protection	24 V DC /no explosion protection/G3/ HKU	24 V DC /no explosion protection/G3	24 V DC /explosion protection	24 V DC /explosion protection/G3

● FIO Node Kit (ESB Bus Node Unit) A2NBX1-□□□□□□

A2NBX1-□01□□□□ (100-120 V AC)

Contents of the model for ordering multi-products				A2NBX1-□01□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D010000 A2NBX1-S010000	A2NBX1-D010010 A2NBX1-S010010	A2NBX1-D010300 A2NBX1-S010300	A2NBX1-D010310 A2NBX1-S010310	A2NBX1-D011000 A2NBX1-S011000	A2NBX1-D011010 A2NBX1-S011010	A2NBX1-D011300 A2NBX1-S011300	A2NBX1-D011310 A2NBX1-S011310
Base Plate	A2BE2D	-S000	no explosion protection	1	1						
		-S030	no explosion protection/G3			1	1				
		-S100	explosion protection					1	1		
		-S130	explosion protection/G3							1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection	1 / 2	1 / 2						
		-51	100-120 V AC /no explosion protection/G3			1 / 2	1 / 2				
		-E0	100-120 V AC/explosion protection					1 / 2	1 / 2		
		-E1	100-120 V AC/explosion protection/G3							1 / 2	1 / 2
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
ESB Bus Interface Slave Module	SB401	-50	no explosion protection	1 / 2	1 / 2						
		-53	no explosion protection/G3			1 / 2	1 / 2				
		-E0	explosion protection					1 / 2	1 / 2		
		-E3	explosion protection/G3							1 / 2	1 / 2
ESB Bus Adapter (for SB401)	A2EE1A	-N	Connector unit	1 / 2		1 / 2		1 / 2		1 / 2	
		-T	Connector unit with terminator		1 / 2		1 / 2		1 / 2		1 / 2
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC /no explosion protection/ Connector unit	100-120 V AC /no explosion protection/ Connector unit with terminator	100-120 V AC /no explosion protection/ G3/Connector unit	100-120 V AC /no explosion protection/ G3/Connector unit with terminator	100-120 V AC/explosion protection/ Connector unit	100-120 V AC/explosion protection/ Connector unit with terminator	100-120 V AC/explosion protection/G3/ Connector unit	100-120 V AC/explosion protection/G3/ Connector unit with terminator

A2NBX1-□02□□□□ (220-240 V AC)

Contents of the model for ordering multi-products				A2NBX1-□02□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-S020000	A2NBX1-D020010	A2NBX1-S020300	A2NBX1-D020310	A2NBX1-S021000	A2NBX1-D021010	A2NBX1-S021300	A2NBX1-D021310
Base Plate	A2BE2D	-S000	no explosion protection	1	1						
		-S030	no explosion protection/G3			1	1				
		-S100	explosion protection					1	1		
		-S130	explosion protection/G3							1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection	1 / 2	1 / 2						
		-51	220-240 V AC /no explosion protection/G3			1 / 2	1 / 2				
		-E0	220-240 V AC/explosion protection					1 / 2	1 / 2		
		-E1	220-240 V AC/explosion protection/G3							1 / 2	1 / 2
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
ESB Bus Interface Slave Module	SB401	-50	no explosion protection	1 / 2	1 / 2						
		-53	no explosion protection/G3			1 / 2	1 / 2				
		-E0	explosion protection					1 / 2	1 / 2		
		-E3	explosion protection/G3							1 / 2	1 / 2
ESB Bus Adapter (for SB401)	A2EE1A	-N	Connector unit	1 / 2		1 / 2		1 / 2		1 / 2	
		-T	Connector unit with terminator		1 / 2		1 / 2		1 / 2		1 / 2
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC /no explosion protection/Connector unit	220-240 V AC /no explosion protection/Connector unit with terminator	220-240 V AC /no explosion protection/G3/Connector unit	220-240 V AC /no explosion protection/G3/Connector unit with terminator	220-240 V AC/explosion protection/Connector unit	220-240 V AC/explosion protection/Connector unit with terminator	220-240 V AC/explosion protection/G3/Connector unit	220-240 V AC/explosion protection/G3/Connector unit with terminator

A2NBX1-□04□□□□ (24V DC)

Contents of the model for ordering multi-products				A2NBX1-□04□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D040000 A2NBX1-S040000	A2NBX1-D040010 A2NBX1-S040010	A2NBX1-D040300 A2NBX1-S040300	A2NBX1-D040310 A2NBX1-S040310	A2NBX1-D041000 A2NBX1-S041000	A2NBX1-D041010 A2NBX1-S041010	A2NBX1-D041300 A2NBX1-S041300	A2NBX1-D041310 A2NBX1-S041310
Base Plate	A2BE2D	-S000	no explosion protection	1	1						
		-S030	no explosion protection/G3			1	1				
		-S100	explosion protection					1	1		
		-S130	explosion protection/G3							1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection	1 / 2	1 / 2						
		-51	24 V DC /no explosion protection/G3			1 / 2	1 / 2				
		-E0	24 V DC /explosion protection					1 / 2	1 / 2		
		-E1	24 V DC /explosion protection/G3							1 / 2	1 / 2
ESB Bus Interface Slave Module	SB401	-50	no explosion protection	1 / 2	1 / 2						
		-53	no explosion protection/G3			1 / 2	1 / 2				
		-E0	explosion protection					1 / 2	1 / 2		
		-E3	explosion protection/G3							1 / 2	1 / 2
ESB Bus Adapter (for SB401)	A2EE1A	-N	Connector unit	1 / 2		1 / 2		1 / 2		1 / 2	
		-T	Connector unit with terminator		1 / 2		1 / 2		1 / 2		1 / 2
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				24 V DC /no explosion protection/Connector unit	24 V DC /no explosion protection/Connector unit with terminator	24 V DC /no explosion protection/G3/Connector unit	24 V DC /no explosion protection/G3/Connector unit with terminator	24 V DC /explosion protection/Connector unit	24 V DC /explosion protection/Connector unit with terminator	24 V DC /explosion protection/G3/Connector unit	24 V DC /explosion protection/G3/Connector unit with terminator

● FIO Node Kit (Optical ESB Bus Node Unit for 5km) A2NBX1-□1□□□□□

A2NBX1-□11□□□□ (100-120 V AC)

Contents of the model for ordering multi-products				A2NBX1-□11□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D110000 A2NBX1-S110000	A2NBX1-D110010 A2NBX1-S110010	A2NBX1-D110020 A2NBX1-S110020	A2NBX1-D110030 A2NBX1-S110030	A2NBX1-D110300 A2NBX1-S110300	A2NBX1-D110310 A2NBX1-S110310	A2NBX1-D110320 A2NBX1-S110320	A2NBX1-D110330 A2NBX1-S110330
Base Plate	A2BE2D	-S000	no explosion protection	1	1	1	1				
		-S030	no explosion protection/G3					1	1	1	1
		-S100	explosion protection								
		-S130	explosion protection/G3								
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-51	100-120 V AC /no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km	ANT502	-5E	no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-5F	no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-EE	explosion protection								
		-EF	explosion protection/G3								
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NH	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC /no explosion protection/ Connector unit	100-120 V AC /no explosion protection/ Connector unit with terminator	100-120 V AC /no explosion protection/ Connector unit/HKU	100-120 V AC /no explosion protection/ Connector unit with terminator/HKU	100-120 V AC /no explosion protection/ G3/Connector unit	100-120 V AC /no explosion protection/ G3/Connector unit with terminator	100-120 V AC /no explosion protection/ G3/Connector unit/HKU	100-120 V AC /no explosion protection/ G3/Connector unit with terminator/HKU

Contents of the model for ordering multi-products				A2NBX1-□11□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D111000 A2NBX1-S111000	A2NBX1-D111010 A2NBX1-S111010	A2NBX1-D111020 A2NBX1-S111020	A2NBX1-D111030 A2NBX1-S111030	A2NBX1-D111300 A2NBX1-S111300	A2NBX1-D111310 A2NBX1-S111310	A2NBX1-D111320 A2NBX1-S111320	A2NBX1-D111330 A2NBX1-S111330
Base Plate	A2BE2D	-S000	no explosion protection								
		-S030	no explosion protection/G3								
		-S100	explosion protection	1	1	1	1				
		-S130	explosion protection/G3					1	1	1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-E1	100-120 V AC/explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km	ANT502	-5E	no explosion protection								
		-5F	no explosion protection/G3								
		-EE	explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-EF	explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NH	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC/explosion protection/Connector unit	100-120 V AC/explosion protection/Connector unit with terminator	100-120 V AC/explosion protection/Connector unit/HKU	100-120 V AC/explosion protection/Connector unit with terminator/HKU	100-120 V AC/explosion protection/G3/Connector unit	100-120 V AC/explosion protection/G3/Connector unit with terminator	100-120 V AC/explosion protection/G3/Connector unit/HKU	100-120 V AC/explosion protection/G3/Connector unit with terminator/HKU

A2NBX1-□12□□□□ (220-240 V AC)

Contents of the model for ordering multi-products				A2NBX1-□12□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D120000 A2NBX1-S120000	A2NBX1-D120010 A2NBX1-S120010	A2NBX1-D120020 A2NBX1-S120020	A2NBX1-D120030 A2NBX1-S120030	A2NBX1-D120300 A2NBX1-S120300	A2NBX1-D120310 A2NBX1-S120310	A2NBX1-D120320 A2NBX1-S120320	A2NBX1-D120330 A2NBX1-S120330
Base Plate	A2BE2D	-S000	no explosion protection	1	1	1	1				
		-S030	no explosion protection/G3					1	1	1	1
		-S100	explosion protection								
		-S130	explosion protection/G3								
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-51	220-240 V AC /no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km	ANT502	-5E	no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-5F	no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-EE	explosion protection								
		-EF	explosion protection/G3								
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NH	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC /no explosion protection/ Connector unit	220-240 V AC /no explosion protection/ Connector unit with terminator	220-240 V AC /no explosion protection/ Connector unit/HKU	220-240 V AC /no explosion protection/ Connector unit with terminator/HKU	220-240 V AC /no explosion protection/G3/ Connector unit	220-240 V AC /no explosion protection/G3/ Connector unit with terminator	220-240 V AC /no explosion protection/G3/ Connector unit/HKU	220-240 V AC /no explosion protection/G3/ Connector unit with terminator/HKU

Contents of the model for ordering multi-products				A2NBX1-□12□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D121000 A2NBX1-S121000	A2NBX1-D121010 A2NBX1-S121010	A2NBX1-D121020 A2NBX1-S121020	A2NBX1-D121030 A2NBX1-S121030	A2NBX1-D121300 A2NBX1-S121300	A2NBX1-D121310 A2NBX1-S121310	A2NBX1-D121320 A2NBX1-S121320	A2NBX1-D121330 A2NBX1-S121330
Base Plate	A2BE2D	-S000	no explosion protection								
		-S030	no explosion protection/G3								
		-S100	explosion protection	1	1	1	1				
		-S130	explosion protection/G3					1	1	1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-E1	220-240 V AC/explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km	ANT502	-5E	no explosion protection								
		-5F	no explosion protection/G3								
		-EE	explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-EF	explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NH	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC/explosion protection/Connector unit	220-240 V AC/explosion protection/Connector unit with terminator	220-240 V AC/explosion protection/Connector unit/HKU	220-240 V AC/explosion protection/Connector unit with terminator/HKU	220-240 V AC/explosion protection/G3/Connector unit	220-240 V AC/explosion protection/G3/Connector unit with terminator	220-240 V AC/explosion protection/G3/Connector unit/HKU	220-240 V AC/explosion protection/G3/Connector unit with terminator/HKU

A2NBX1-□14□□□□ (24V DC)

Contents of the model for ordering multi-products				A2NBX1-□14□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D140000 A2NBX1-S140000	A2NBX1-D140010 A2NBX1-S140010	A2NBX1-D140020 A2NBX1-S140020	A2NBX1-D140030 A2NBX1-S140030	A2NBX1-D140300 A2NBX1-S140300	A2NBX1-D140310 A2NBX1-S140310	A2NBX1-D140320 A2NBX1-S140320	A2NBX1-D140330 A2NBX1-S140330
Base Plate	A2BE2D	-S000	no explosion protection	1	1	1	1				
		-S030	no explosion protection/G3					1	1	1	1
		-S100	explosion protection								
		-S130	explosion protection/G3								
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-51	24 V DC /no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km	ANT502	-5E	no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-5F	no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-EE	explosion protection								
		-EF	explosion protection/G3								
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NH	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				24 V DC /no explosion protection/Connector unit	24 V DC /no explosion protection/Connector unit with terminator	24 V DC /no explosion protection/Connector unit/HKU	24 V DC /no explosion protection/Connector unit with terminator/HKU	24 V DC /no explosion protection/G3/Connector unit	24 V DC /no explosion protection/G3/Connector unit with terminator	24 V DC /no explosion protection/G3/Connector unit/HKU	24 V DC /no explosion protection/G3/Connector unit with terminator/HKU

Contents of the model for ordering multi-products				A2NBX1-□14□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D141000 A2NBX1-S141000	A2NBX1-D141010 A2NBX1-S141010	A2NBX1-D141020 A2NBX1-S141020	A2NBX1-D141030 A2NBX1-S141030	A2NBX1-D141300 A2NBX1-S141300	A2NBX1-D141310 A2NBX1-S141310	A2NBX1-D141320 A2NBX1-S141320	A2NBX1-D141330 A2NBX1-S141330
Base Plate	A2BE2D	-S000	no explosion protection								
		-S030	no explosion protection/G3								
		-S100	explosion protection	1	1	1	1				
		-S130	explosion protection/G3					1	1	1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-E1	24 V DC /explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
Optical ESB Bus Repeater Slave Module For 5 km	ANT502	-5E	no explosion protection								
		-5F	no explosion protection/G3								
		-EE	explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-EF	explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NH	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				24 V DC /explosion protection/Connector unit	24 V DC /explosion protection/Connector unit with terminator	24 V DC /explosion protection/Connector unit/HKU	24 V DC /explosion protection/Connector unit with terminator/HKU	24 V DC /explosion protection/Connector unit	24 V DC /explosion protection/G3/Connector unit with terminator	24 V DC /explosion protection/G3/Connector unit/HKU	24 V DC /explosion protection/G3/Connector unit with terminator/HKU

● FIO Node Kit (Optical ESB Bus Node Unit for 5km to 50km) A2NBX1-□21□□□□□

A2NBX1-□21□□□□ (100-120 V AC)

Contents of the model for ordering multi-products				A2NBX1-□21□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D210000 A2NBX1-S210000	A2NBX1-D210010 A2NBX1-S210010	A2NBX1-D210020 A2NBX1-S210020	A2NBX1-D210030 A2NBX1-S210030	A2NBX1-D210300 A2NBX1-S210300	A2NBX1-D210310 A2NBX1-S210310	A2NBX1-D210320 A2NBX1-S210320	A2NBX1-D210330 A2NBX1-S210330
Base Plate	A2BE2D	-S000	no explosion protection	1	1	1	1				
		-S030	no explosion protection/G3					1	1	1	1
		-S100	explosion protection								
		-S130	explosion protection/G3								
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-51	100-120 V AC /no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km to 5 km	ANT512	-5E	no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-5F	no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-EE	explosion protection								
		-EF	explosion protection/G3								
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NN	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC /no explosion protection/ Connector unit	100-120 V AC /no explosion protection/ Connector unit with terminator	100-120 V AC /no explosion protection/ Connector unit/HKU	100-120 V AC /no explosion protection/ Connector unit with terminator/HKU	100-120 V AC /no explosion protection/G3/ Connector unit	100-120 V AC /no explosion protection/G3/ Connector unit with terminator	100-120 V AC /no explosion protection/G3/ Connector unit/HKU	100-120 V AC /no explosion protection/G3/ Connector unit with terminator/HKU

Contents of the model for ordering multi-products				A2NBX1-□21□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D21I1000 A2NBX1-S21I1000	A2NBX1-D21I010 A2NBX1-S21I010	A2NBX1-D21I020 A2NBX1-S21I020	A2NBX1-D21I030 A2NBX1-S21I030	A2NBX1-D21I300 A2NBX1-S21I300	A2NBX1-D21I310 A2NBX1-S21I310	A2NBX1-D21I320 A2NBX1-S21I320	A2NBX1-D21I330 A2NBX1-S21I330
Base Plate	A2BE2D	-S000	no explosion protection								
		-S030	no explosion protection/G3								
		-S100	explosion protection	1	1	1	1				
		-S130	explosion protection/G3					1	1	1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-E1	100-120 V AC/explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km to 5 km	ANT512	-5E	no explosion protection								
		-5F	no explosion protection/G3								
		-EE	explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-EF	explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NN	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1/2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC/explosion protection/Connector unit	100-120 V AC/explosion protection/Connector unit with terminator	100-120 V AC/explosion protection/Connector unit/HKU	100-120 V AC/explosion protection/Connector unit with terminator/HKU	100-120 V AC/explosion protection/G3/Connector unit	100-120 V AC/explosion protection/G3/Connector unit with terminator	100-120 V AC/explosion protection/G3/Connector unit/HKU	100-120 V AC/explosion protection/G3/Connector unit with terminator/HKU

A2NBX1-□22□□□□ (220-240 V AC)

Contents of the model for ordering multi-products				A2NBX1-□22□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D220000 A2NBX1-S220000	A2NBX1-D220010 A2NBX1-S220010	A2NBX1-D220020 A2NBX1-S220020	A2NBX1-D220030 A2NBX1-S220030	A2NBX1-D220300 A2NBX1-S220300	A2NBX1-D220310 A2NBX1-S220310	A2NBX1-D220320 A2NBX1-S220320	A2NBX1-D220330 A2NBX1-S220330
Base Plate	A2BE2D	-S000	no explosion protection	1	1	1	1				
		-S030	no explosion protection/G3					1	1	1	1
		-S100	explosion protection								
		-S130	explosion protection/G3								
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-51	220-240 V AC /no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km to 5 km	ANT512	-5E	no explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-5F	no explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
		-EE	explosion protection								
		-EF	explosion protection/G3								
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NN	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC /no explosion protection/ Connector unit	220-240 V AC /no explosion protection/ Connector unit with terminator	220-240 V AC /no explosion protection/ Connector unit/HKU	220-240 V AC /no explosion protection/ Connector unit with terminator/HKU	220-240 V AC /no explosion protection/G3/ Connector unit	220-240 V AC /no explosion protection/G3/ Connector unit with terminator	220-240 V AC /no explosion protection/G3/ Connector unit/HKU	220-240 V AC /no explosion protection/G3/ Connector unit with terminator/HKU

Contents of the model for ordering multi-products				A2NBX1-□22□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D221000 A2NBX1-S221000	A2NBX1-D221010 A2NBX1-S221010	A2NBX1-D221020 A2NBX1-S221020	A2NBX1-D221030 A2NBX1-S221030	A2NBX1-D221300 A2NBX1-S221300	A2NBX1-D221310 A2NBX1-S221310	A2NBX1-D221320 A2NBX1-S221320	A2NBX1-D221330 A2NBX1-S221330
Base Plate	A2BE2D	-S000	no explosion protection								
		-S030	no explosion protection/G3								
		-S100	explosion protection	1	1	1	1				
		-S130	explosion protection/G3					1	1	1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-E1	220-240 V AC/explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km to 5 km	ANT512	-5E	no explosion protection								
		-5F	no explosion protection/G3								
		-EE	explosion protection	1 / 2	1 / 2	1 / 2	1 / 2				
		-EF	explosion protection/G3					1 / 2	1 / 2	1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1 / 2				1 / 2	
		-NN	Connector unit	1 / 2				1 / 2			
		-TH	Connector unit with terminator/HKU				1 / 2				1 / 2
		-TN	Connector unit with terminator		1 / 2				1 / 2		
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC/explosion protection/Connector unit	220-240 V AC/explosion protection/Connector unit with terminator	220-240 V AC/explosion protection/Connector unit/HKU	220-240 V AC/explosion protection/Connector unit with terminator/HKU	220-240 V AC/explosion protection/G3/Connector unit	220-240 V AC/explosion protection/G3/Connector unit with terminator	220-240 V AC/explosion protection/G3/Connector unit/HKU	220-240 V AC/explosion protection/G3/Connector unit with terminator/HKU

A2NBX1-□24□□□□ (24V DC)

Contents of the model for ordering multi-products				A2NBX1-□24□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D240000 A2NBX1-S240000	A2NBX1-D240010 A2NBX1-S240010	A2NBX1-D240020 A2NBX1-S240020	A2NBX1-D240030 A2NBX1-S240030	A2NBX1-D240300 A2NBX1-S240300	A2NBX1-D240310 A2NBX1-S240310	A2NBX1-D240320 A2NBX1-S240320	A2NBX1-D240330 A2NBX1-S240330
Base Plate	A2BE2D	-S000	no explosion protection	1	1	1	1				
		-S030	no explosion protection/G3					1	1	1	1
		-S100	explosion protection								
		-S130	explosion protection/G3								
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection	1/2	1/2	1/2	1/2				
		-51	24 V DC /no explosion protection/G3					1/2	1/2	1/2	1/2
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 5 km to 5 km	ANT512	-5E	no explosion protection	1/2	1/2	1/2	1/2				
		-5F	no explosion protection/G3					1/2	1/2	1/2	1/2
		-EE	explosion protection								
		-EF	explosion protection/G3								
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1/2				1/2	
		-NN	Connector unit	1/2				1/2			
		-TH	Connector unit with terminator/HKU				1/2				1/2
		-TN	Connector unit with terminator		1/2				1/2		
Dummy Cover	ADCV01		For slot B2	1/0	1/0	1/0	1/0	1/0	1/0	1/0	1/0
	ADCV02		For slot P2	1/0	1/0	1/0	1/0	1/0	1/0	1/0	1/0
				24 V DC /no explosion protection/ Connector unit	24 V DC /no explosion protection/ Connector unit with terminator	24 V DC /no explosion protection/ Connector unit/HKU	24 V DC /no explosion protection/ Connector unit with terminator/HKU	24 V DC /no explosion protection/G3/ Connector unit	24 V DC /no explosion protection/G3/ Connector unit with terminator	24 V DC /no explosion protection/G3/ Connector unit/HKU	24 V DC /no explosion protection/G3/ Connector unit with terminator/HKU

Contents of the model for ordering multi-products				A2NBX1-□24□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D241000 A2NBX1-S241000	A2NBX1-D241010 A2NBX1-S241010	A2NBX1-D241020 A2NBX1-S241020	A2NBX1-D241030 A2NBX1-S241030	A2NBX1-D241300 A2NBX1-S241300	A2NBX1-D241310 A2NBX1-S241310	A2NBX1-D241320 A2NBX1-S241320	A2NBX1-D241330 A2NBX1-S241330
Base Plate	A2BE2D	-S000	no explosion protection								
		-S030	no explosion protection/G3								
		-S100	explosion protection	1	1	1	1				
		-S130	explosion protection/G3					1	1	1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection	1/2	1/2	1/2	1/2				
		-E1	24 V DC /explosion protection/G3					1/2	1/2	1/2	1/2
Optical ESB Bus Repeater Slave Module For 5 km to 5 km	ANT512	-5E	no explosion protection								
		-5F	no explosion protection/G3								
		-EE	explosion protection	1/2	1/2	1/2	1/2				
		-EF	explosion protection/G3					1/2	1/2	1/2	1/2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU			1/2				1/2	
		-NN	Connector unit	1/2				1/2			
		-TH	Connector unit with terminator/HKU				1/2				1/2
		-TN	Connector unit with terminator		1/2				1/2		
Dummy Cover	ADCV01		For slot B2	1/0	1/0	1/0	1/0	1/0	1/0	1/0	1/0
	ADCV02		For slot P2	1/0	1/0	1/0	1/0	1/0	1/0	1/0	1/0
				24 V DC /explosion protection/Connector unit	24 V DC /explosion protection/Connector unit with terminator	24 V DC /explosion protection/Connector unit /HKU	24 V DC /explosion protection/Connector unit with terminator/HKU	24 V DC /explosion protection/Connector unit	24 V DC /explosion protection/G3/Connector unit with terminator	24 V DC /explosion protection/G3/Connector unit/HKU	24 V DC /explosion protection/G3/Connector unit with terminator/HKU

● FIO Node Kit (Optical ESB Bus Node Unit for 4km MMF) A2NBX1-□3□□□□□

A2NBX1-□31□□□□ (100-120 V AC)

Contents of the model for ordering multi-products				A2NBX1-□31□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D310000 A2NBX1-S310000	A2NBX1-D310010 A2NBX1-S310010	A2NBX1-D310300 A2NBX1-S310300	A2NBX1-D310310 A2NBX1-S310310	A2NBX1-D311000 A2NBX1-S311000	A2NBX1-D311010 A2NBX1-S311010	A2NBX1-D311300 A2NBX1-S311300	A2NBX1-D311310 A2NBX1-S311310
Base Plate	A2BE2D	-S000	no explosion protection	1	1						
		-S030	no explosion protection/G3			1	1				
		-S100	explosion protection					1	1		
		-S130	explosion protection/G3							1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection	1 / 2	1 / 2						
		-51	100-120 V AC /no explosion protection/G3			1 / 2	1 / 2				
		-E0	100-120 V AC/explosion protection					1 / 2	1 / 2		
		-E1	100-120 V AC/explosion protection/G3							1 / 2	1 / 2
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 4km MMF	ANT522	-50	no explosion protection	1 / 2	1 / 2						
		-53	no explosion protection/G3			1 / 2	1 / 2				
		-E0	explosion protection					1 / 2	1 / 2		
		-E3	explosion protection/G3							1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU								
		-NN	Connector unit	1 / 2		1 / 2		1 / 2		1 / 2	
		-TH	Connector unit with terminator/HKU								
		-TN	Connector unit with terminator		1 / 2		1 / 2		1 / 2		1 / 2
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC /no explosion protection/ Connector unit	100-120 V AC /no explosion protection/ Connector unit with terminator	100-120 V AC /no explosion protection/G3/ Connector unit	100-120 V AC /no explosion protection/G3/ Connector unit with terminator	100-120 V AC/explosion protection/ Connector unit	100-120 V AC/explosion protection/ Connector unit with terminator	100-120 V AC/explosion protection/G3/ Connector unit	100-120 V AC/explosion protection/G3/ Connector unit with terminator

A2NBX1-□32□□□□ (220-240 V AC)

Contents of the model for ordering multi-products				A2NBX1-□32□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D321310 A2NBX1-S321310	A2NBX1-D321300 A2NBX1-S321300	A2NBX1-D321010 A2NBX1-S321010	A2NBX1-D321000 A2NBX1-S321000	A2NBX1-D320310 A2NBX1-S320310	A2NBX1-D320300 A2NBX1-S320300	A2NBX1-D320010 A2NBX1-S320010	A2NBX1-D320000 A2NBX1-S320000
Base Plate	A2BE2D	-S000	no explosion protection	1	1						
		-S030	no explosion protection/G3			1	1				
		-S100	explosion protection				1	1			
		-S130	explosion protection/G3							1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection	1 / 2	1 / 2						
		-51	220-240 V AC /no explosion protection/G3			1 / 2	1 / 2				
		-E0	220-240 V AC/explosion protection				1 / 2	1 / 2			
		-E1	220-240 V AC/explosion protection/G3							1 / 2	1 / 2
	PW484	-50	24 V DC /no explosion protection								
		-51	24 V DC /no explosion protection/G3								
		-E0	24 V DC /explosion protection								
		-E1	24 V DC /explosion protection/G3								
Optical ESB Bus Repeater Slave Module For 4km MMF	ANT522	-50	no explosion protection	1 / 2	1 / 2						
		-53	no explosion protection/G3			1 / 2	1 / 2				
		-E0	explosion protection				1 / 2	1 / 2			
		-E3	explosion protection/G3							1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU								
		-NN	Connector unit	1 / 2		1 / 2		1 / 2		1 / 2	
		-TH	Connector unit with terminator/HKU								
		-TN	Connector unit with terminator		1 / 2		1 / 2			1 / 2	1 / 2
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC /no explosion protection/ Connector unit	220-240 V AC /no explosion protection/ Connector unit with terminator	220-240 V AC /no explosion protection/G3/ Connector unit	220-240 V AC /no explosion protection/G3/ Connector unit with terminator	220-240 V AC /no explosion protection/G3/ Connector unit	220-240 V AC /no explosion protection/G3/ Connector unit with terminator	220-240 V AC/explosion protection/Connector unit	220-240 V AC/explosion protection/Connector unit with terminator

A2NBX1-□34□□□□ (24V DC)

Contents of the model for ordering multi-products				A2NBX1-□34□□□□ MS-CODE							
Category	Model	MS-CODE	Description	A2NBX1-D340000 A2NBX1-S340000	A2NBX1-D340010 A2NBX1-S340010	A2NBX1-D340300 A2NBX1-S340300	A2NBX1-D340310 A2NBX1-S340310	A2NBX1-D341000 A2NBX1-S341000	A2NBX1-D341010 A2NBX1-S341010	A2NBX1-D341300 A2NBX1-S341300	A2NBX1-D341310 A2NBX1-S341310
Base Plate	A2BE2D	-S000	no explosion protection	1	1						
		-S030	no explosion protection/G3			1	1				
		-S100	explosion protection					1	1		
		-S130	explosion protection/G3							1	1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection								
		-51	100-120 V AC /no explosion protection/G3								
		-E0	100-120 V AC/explosion protection								
		-E1	100-120 V AC/explosion protection/G3								
	PW482	-50	220-240 V AC /no explosion protection								
		-51	220-240 V AC /no explosion protection/G3								
		-E0	220-240 V AC/explosion protection								
		-E1	220-240 V AC/explosion protection/G3								
	PW484	-50	24 V DC /no explosion protection	1 / 2	1 / 2						
		-51	24 V DC /no explosion protection/G3			1 / 2	1 / 2				
		-E0	24 V DC /explosion protection					1 / 2	1 / 2		
		-E1	24 V DC /explosion protection/G3							1 / 2	1 / 2
Optical ESB Bus Repeater Slave Module For 4km MMF	ANT522	-50	no explosion protection	1 / 2	1 / 2						
		-53	no explosion protection/G3			1 / 2	1 / 2				
		-E0	explosion protection					1 / 2	1 / 2		
		-E3	explosion protection/G3							1 / 2	1 / 2
ESB Bus Adapter (for ANT5□2)	A2EE3A	-NH	Connector unit/HKU								
		-NN	Connector unit	1 / 2		1 / 2		1 / 2		1 / 2	
		-TH	Connector unit with terminator/HKU								
		-TN	Connector unit with terminator		1 / 2		1 / 2		1 / 2		1 / 2
Dummy Cover	ADCV01		For slot B2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0	1 / 0
				24 V DC /no explosion protection/Connector unit	24 V DC /no explosion protection/Connector unit with terminator	24 V DC /no explosion protection/G3/Connector unit	24 V DC /no explosion protection/G3/Connector unit with terminator	24 V DC /explosion protection/Connector unit	24 V DC /explosion protection/Connector unit with terminator	24 V DC /explosion protection/G3/Connector unit	24 V DC /explosion protection/G3/Connector unit with terminator

● FIO Node Kit (Optical ESB Bus Repeater Unit) A2NBX1-□4□□□4□

A2NBX1-□41□□4□ (100-120 V AC)

Contents of the model for ordering multi-products				A2NBX1-□41□□4□ MS-CODE			
Category	Model	MS-CODE	Description	A2NBX1-D410040 A2NBX1-S410040	A2NBX1-D410340 A2NBX1-S410340	A2NBX1-D411040 A2NBX1-S411040	A2NBX1-D411340 A2NBX1-S411340
Base Plate	A2BE2D	-S000	no explosion protection	1			
		-S030	no explosion protection/G3		1		
		-S100	explosion protection			1	
		-S130	explosion protection/G3				1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection	1 / 2			
		-51	100-120 V AC /no explosion protection/G3		1 / 2		
		-E0	100-120 V AC/explosion protection			1 / 2	
		-E1	100-120 V AC/explosion protection/G3				1 / 2
	PW482	-50	220-240 V AC /no explosion protection				
		-51	220-240 V AC /no explosion protection/G3				
		-E0	220-240 V AC/explosion protection				
		-E1	220-240 V AC/explosion protection/G3				
	PW484	-50	24 V DC /no explosion protection				
		-51	24 V DC /no explosion protection/G3				
		-E0	24 V DC /explosion protection				
		-E1	24 V DC /explosion protection/G3				
Dummy Cover	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0
				100-120 V AC /no explosion protection	100-120 V AC /no explosion protection/G3	100-120 V AC/explosion protection	100-120 V AC/explosion protection/G3

A2NBX1-□42□□4□ (220-240 V AC)

Contents of the model for ordering multi-products				A2NBX1-□42□□4□ MS-CODE			
Category	Model	MS-CODE	Description	A2NBX1-D420040 A2NBX1-S420040	A2NBX1-D420340 A2NBX1-S420340	A2NBX1-D421040 A2NBX1-S421040	A2NBX1-D421340 A2NBX1-S421340
Base Plate	A2BE2D	-S000	no explosion protection	1			
		-S030	no explosion protection/G3		1		
		-S100	explosion protection			1	
		-S130	explosion protection/G3				1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection				
		-51	100-120 V AC /no explosion protection/G3				
		-E0	100-120 V AC/explosion protection				
		-E1	100-120 V AC/explosion protection/G3				
	PW482	-50	220-240 V AC /no explosion protection	1 / 2			
		-51	220-240 V AC /no explosion protection/G3		1 / 2		
		-E0	220-240 V AC/explosion protection			1 / 2	
		-E1	220-240 V AC/explosion protection/G3				1 / 2
	PW484	-50	24 V DC /no explosion protection				
		-51	24 V DC /no explosion protection/G3				
		-E0	24 V DC /explosion protection				
		-E1	24 V DC /explosion protection/G3				
Dummy Cover	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0
				220-240 V AC /no explosion protection	220-240 V AC /no explosion protection/G3	220-240 V AC/explosion protection	220-240 V AC/explosion protection/G3

A2NBX1-□44□□4□ (24V DC)

Contents of the model for ordering multi-products				A2NBX1-□44□□4□ MS-CODE			
Category	Model	MS-CODE	Description	A2NBX1-D440040 A2NBX1-S440040	A2NBX1-D440340 A2NBX1-S440340	A2NBX1-D441040 A2NBX1-S441040	A2NBX1-D441340 A2NBX1-S441340
Base Plate	A2BE2D	-S000	no explosion protection	1			
		-S030	no explosion protection/G3		1		
		-S100	explosion protection			1	
		-S130	explosion protection/G3				1
Power Supply Module	PW481	-50	100-120 V AC /no explosion protection				
		-51	100-120 V AC /no explosion protection/G3				
		-E0	100-120 V AC/explosion protection				
		-E1	100-120 V AC/explosion protection/G3				
	PW482	-50	220-240 V AC /no explosion protection				
		-51	220-240 V AC /no explosion protection/G3				
		-E0	220-240 V AC/explosion protection				
		-E1	220-240 V AC/explosion protection/G3				
	PW484	-50	24 V DC /no explosion protection	1 / 2			
		-51	24 V DC /no explosion protection/G3		1 / 2		
		-E0	24 V DC /explosion protection			1 / 2	
		-E1	24 V DC /explosion protection/G3				1 / 2
Dummy Cover	ADCV02		For slot P2	1 / 0	1 / 0	1 / 0	1 / 0
				24 V DC /no explosion protection	24 V DC /no explosion protection/G3	24 V DC /explosion protection	24 V DC /explosion protection/G3

● AEPV7D Input Power Cable Kit (for A2CUKT4) A2CUX1

A2CUX1-1□□□ (for Single Power Supply)

Contents of the model for ordering multi-products			A2CUX1-1□□□ MS-CODE								
Category	Part No	Description	A2CUX1-A000	A2CUX1-B000	A2CUX1-C000	A2CUX1-D000	A2CUX1-E000	A2CUX1-F000	A2CUX1-G000	A2CUX1-H000	A2CUX1-J000
For front of cabinet	S9101UW	100V AC/220V AC, Mark Band:1-1	1	1		1	1				
	S9102UW	100V AC/220V AC, Mark Band:L1-L1									
	S9103UW	100V AC/220V AC, Mark Band:R1-R1									
	S9104UW	24 V DC, Mark Band:1-1							1	1	
	S9105UW	24 V DC, Mark Band:3-3							1	1	
	S9106UW	24 V DC, Mark Band:L1-L1									
	S9107UW	24 V DC, Mark Band:R1-R1									
	S9108UW	24 V DC, Mark Band:L3-L3									
	S9109UW	24 V DC, Mark Band:R3-R3									
For rear of cabinet	S9201UW	100V AC/220V AC, Mark Band:3-3	1		1	1		1			
	S9202UW	100V AC/220V AC, Mark Band:L3-L3									
	S9203UW	100V AC/220V AC, Mark Band:R3-R3									
	S9204UW	24 V DC, Mark Band:2-2							1		1
	S9205UW	24 V DC, Mark Band:4-4							1		1
	S9206UW	24 V DC, Mark Band:L2-L2									
	S9207UW	24 V DC, Mark Band:R2-R2									
	S9208UW	24 V DC, Mark Band:L4-L4									
	S9209UW	24 V DC, Mark Band:R4-R4									
			Single /100-120 V AC/Front, Rear	Single /100-120 V AC/Front	Single /100-120 V AC/Rear	Single /220-240 V AC/Front, Rear	Single /220-240 V AC/Front	Single /220-240 V AC/Rear	Single /24 V DC/Front, Rear	Single /24 V DC/Front	Single /24 V DC/Rear

A2CUX1-2□□□ (for Dual Power Supply)

Contents of the model for ordering multi-products			A2CUX1-2□□□ MS-CODE								
Category	Part No	Description	A2CUX1-K000	A2CUX1-L000	A2CUX1-M000	A2CUX1-N000	A2CUX1-P000	A2CUX1-Q000	A2CUX1-R000	A2CUX1-S000	A2CUX1-T000
For front of cabinet	S9101UW	100 V AC/220V AC, Mark Band:1-1									
	S9102UW	100 V AC/220V AC, Mark Band:L1-L1	1	1		1	1				
	S9103UW	100 V AC/220V AC, Mark Band:R1-R1	1	1		1	1				
	S9104UW	24 V DC, Mark Band:1-1									
	S9105UW	24 V DC, Mark Band:3-3									
	S9106UW	24 V DC, Mark Band:L1-L1							1	1	
	S9107UW	24 V DC, Mark Band:R1-R1							1	1	
	S9108UW	24 V DC, Mark Band:L3-L3							1	1	
	S9109UW	24 V DC, Mark Band:R3-R3							1	1	
For rear of cabinet	S9201UW	100 V AC/220V AC, Mark Band:3-3									
	S9202UW	100 V AC/220V AC, Mark Band:L3-L3	1		1	1		1			
	S9203UW	100 V AC/220V AC, Mark Band:R3-R3	1		1	1		1			
	S9204UW	24 V DC, Mark Band:2-2									
	S9205UW	24 V DC, Mark Band:4-4									
	S9206UW	24 V DC, Mark Band:L2-L2							1		1
	S9207UW	24 V DC, Mark Band:R2-R2							1		1
	S9208UW	24 V DC, Mark Band:L4-L4							1		1
	S9209UW	24 V DC, Mark Band:R4-R4							1		1
			Dual/100-120 V AC/Front, Rear	Dual/100-120 V AC/Front	Dual/100-120 V AC/Rear	Dual/220-240 V AC/Front, Rear	Dual/220-240 V AC/Front	Dual/220-240 V AC/Rear	Dual/24 V DC/Front, Rear	Dual/24 V DC/Front	Dual/24 V DC/Rear

■ TRADEMARK ACKNOWLEDGMENT

The names of corporations, organizations, products and logos herein are either registered trademarks or trademarks of Yokogawa Electric Corporation and their respective holders.